



# Flat Downlight LED

## LIGHTOLIER Flat DL 4" Rd 700lm 90 30K 120V

LIGHTOLIER Flat DL 4" Rd 700lm 90 30K 120V

Philips Lightolier LED flat downlight provides an easy and quick downlight solution without the traditional frame and reflector. Perfect for installation in existing ceilings or new construction with the benefits of energy saving LED technology.

### Product data

General Information	
Lamp Source Code	LED
Colour Temperature	3000K
CRI	90
Mounting	Recessed franse vertaling
Operating and Electrical	
Voltages	120 V
Mechanical and Housing	
Aperture Size Code	4 in
Shape	Round

Initial Performance (IEC Compliant)	
Luminaire Lumens	700
Product Data	
Order product name	LIGHTOLIER Flat DL 4" Rd 700lm 90 30K 120V
Commercial Code	FD4R07930TE1W
Order code	FD4R07930TE1W
Catalog Number Description	LIGHTOLIER Flat DL 4" Rd 700lm 90 30K 120V
Service / Spec Smart	Service Smart (2 Days) North America
Material Nr. (12NC)	LIGU70000001