



# Hexagonal Lantern (L28)

## L28, 100 HPS, CLEAR GLASS AND A SG2 OPTICAL SYSTEM

### L28, 100 HPS, CLEAR GLASS AND A SG2 OPTICAL SYSTEM

Exemplifies Philips Lumec's ability to blend engineering know-how and old-time charm. Nothing has been left to chance in the design of the Hexagonal Lantern. These luminaires are able to fill a space with a warm and reassuring light. Behind the antique-inspired look, the Hexagonal Lantern luminaire reminds us that the past and the present are eternally linked and when combined together in a luminaire, they offer exceptional style. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

#### Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	100
Photometric Distribution Type	Asymmetric
Mounting	Pole Top Pole Arm
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Hexagon

Product Data	
Order product name	L28, 100 HPS, CLEAR GLASS AND A SG2 OPTICAL SYSTEM
Commercial Code	L28-100HPS-GLC-SG2
Order code	L28-100HPS-GLC-SG2
Catalog Number Description	L28, 100 HPS, CLEAR GLASS AND A SG2 OPTICAL SYSTEM
Service / Spec Smart	-
Material Nr. (12NC)	LUM00001718