



Callisto Post Top (CAL1)

Calisto, 70 MH, Type IV, Short, Noncutoff

Calisto, 70 MH, Type IV, Short, Noncutoff

Quality of production and attention to detail ensures its durability, even in the most challenging environments. Inspired by classical and contemporary elements, the Callisto's refined lines cast a timeless light on any project. The combination of two lighting technologies assures maximum light control while contributing to the spirit of a project's settings and preserving the dark skies. The Callisto is the perfect choice for those looking for sophistication, unique styling, and performance. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information	
Lamp Source Code	MH
Lamp Watts	70
Photometric Distribution Type	Type IV
Mounting	Pole Top
Operating and Electrical	
Voltages	120/208/240/277/347 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	Calisto, 70 MH, Type IV, Short, Noncutoff
Commercial Code	CAL1-70MH-G1
Order code	CAL1-70MH-G1
Catalog Number Description	Calisto, 70 MH, Type IV, Short, Noncutoff
Service / Spec Smart	-
Material Nr. (12NC)	LUM70000941