



Callisto Post Top (CAL6)

Calisto, 70 MH, Type II, Short, Semicutoff

Calisto, 70 MH, Type II, Short, Semicutoff

Quality of production and attention to detail ensures its durability, even in the most challenging environments. Inspired by classical and contemporary elements, the Callisto's refined lines cast a timeless light on any project. The combination of two lighting technologies assures maximum light control while contributing to the spirit of a project's settings and preserving the dark skies. The Callisto is the perfect choice for those looking for sophistication, unique styling, and performance. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

| General Information | |
|-------------------------------|-----------------------|
| Lamp Source Code | MH |
| Lamp Watts | 70 |
| Photometric Distribution Type | Type II |
| Mounting | Pole Top |
| Operating and Electrical | |
| Voltages | 120/208/240/277/347 V |
| Mechanical and Housing | |
| Shape | Round |

| Product Data | |
|----------------------------|--|
| Order product name | Calisto, 70 MH, Type II, Short, Semicutoff |
| Commercial Code | CAL6-70MH-G2 |
| Order code | CAL6-70MH-G2 |
| Catalog Number Description | Calisto, 70 MH, Type II, Short, Semicutoff |
| Service / Spec Smart | - |
| Material Nr. (12NC) | LUM70000966 |