



Candela Post Top Large (CAND2)

Candela, 100 HPS, CLEAR POLYCARBONATE GLOBE, SE5 OPTIC

Candela, 100 HPS, CLEAR POLYCARBONATE GLOBE, SE5 OPTIC

Truly versatile the Candela Luminaire with its' traditional style and European inspiration will set the tone and enhance any project. Attention to detail is perhaps the most important aspect of the Candela. From the European inspired nautical design to the wide range of optical systems available, to the wide assortment of complementary products that harmonize with this luminaire, no stone has been left unturned to give decision makers unprecedented flexibility and design options. The Candela is now available with an LED light engine that will provide better longevity and energy savings. The Candela is well suited for nautical environments, roadways, parks and other urban developments. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	100
Mounting	Pole Arm
Operating and Electrical	
Voltages	120/208/240/277/347 V

Mechanical and Housing	
Shape	Round
Product Data	
Order product name	Candela, 100 HPS, CLEAR POLYCARBONATE GLOBE, SE5 OPTIC
Commercial Code	CAND2-100HPS-C-SE5
Order code	CAND2-100HPS-C-SE5
Catalog Number Description	Candela, 100 HPS, CLEAR POLYCARBONATE GLOBE, SE5 OPTIC

Candela Post Top Large (CAND2)

Service / Spec Smart	-
Material Nr. (12NC)	LUM70001007

