



Domus Side Arm Mount (DMS55)

Domus, 100 MH, Type II, Medium, Cutoff, Prismatic Globe

Domus, 100 MH, Type II, Medium, Cutoff, Prismatic Globe

Harmonizing beautifully with virtually any urban setting, the Domus luminaires are representative of the new generation of lighting units. The Domus, Domus 55, and Domus Small are LED luminaires that have undeniable charm. Simplicity, refinement, and elegance, all fuse together to create harmonious beauty through designed equilibrium. Whereas the Domus is a street and public area luminaire, the Domus 55 is well suited for boulevards and parking lots because it is built with high performance optics and has the capacity to receive high wattages. You could install the Domus 55 in a parking lot, and the Domus Small along the paths leading from that parking lot to the building, creating a subtly refined design that balances shape, dimension and proportion. The Domus, Domus 55, and Domus Small are all designed to complement each other and bring balance to any environment. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information	
Lamp Source Code	MH
Lamp Watts	100
Photometric Distribution Type	Type II
Mounting	Pole Arm
Operating and Electrical	
Voltages	120/208/240/277/347/480 V

Mechanical and Housing	
Shape	Round
Product Data	
Order product name	Domus, 100 MH, Type II, Medium, Cutoff, Prismatic Globe
Commercial Code	DMS55-100MH-SHA3M-ACDR
Order code	DMS55-100MH-SHA3M-ACDR
Catalog Number Description	Domus, 100 MH, Type II, Medium, Cutoff, Prismatic Globe
Service / Spec Smart	-

Domus Side Arm Mount (DMS55)

Material Nr. (12NC)	LUM70001382
---------------------	-------------

