



# Opticone Arm Mount (OPC)

## Opticone, 100 HPS, Type II, Medium, Cutoff, Tempered Clear Sag Glass

Opticone, 100 HPS, Type II, Medium, Cutoff, Tempered Clear Sag Glass

Offers visual comfort and environmentally friendly lighting. The Opticone luminaire follows the most innovative lighting trends seen in the world of architectural design. Graceful and distinctive, these luminaires blend seamlessly into unique developments, wherever they cast their glow. The quality of fabrication and the concern for fine details ensure the Opticone's high photometric performance even under the most demanding conditions. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

### Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	100
Photometric Distribution Type	Type II
Mounting	Pole Arm
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	Opticone, 100 HPS, Type II, Medium, Cutoff, Tempered Clear Sag Glass
Commercial Code	OPC-100HPS-SCB3M
Order code	OPC-100HPS-SCB3M
Catalog Number Description	Opticone, 100 HPS, Type II, Medium, Cutoff, Tempered Clear Sag Glass
Service / Spec Smart	-
Material Nr. (12NC)	LUM70001870