



# ClassicStyle Post Top LED (VLR)

ClassicStyle Post Top LED (VLR), 30 LED, Type V, 4000K

ClassicStyle Post Top LED (VLR), 30 LED, Type V, 4000K - 109 lm/W

Now you can enjoy high-performing, energy-saving LED technology without worrying about the harsh glare or pixelization that can occur with LED luminaires. With the full, comfortable glow of new Philips Lumec ClassicStyle Luminaires with ClearGuide Technology, you can breathe new life into nighttime city spaces, strengthen a community bond, and enhance a sense of security throughout the night. This state-of-the-art, outdoor urban post top luminaire use a revolutionary, unique, vertically-oriented light engine that creates transparency during the day; while at night, the center comes to life with full illumination, and free from the glare typically found in standard LED technologies. [<b>Lumec3D: Online 3D Configurator</b></a>](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

## Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
Photometric Distribution Type	Type V
Mounting	Pole Top Pole Arm
Operating and Electrical	
Luminaire Input Watts	35
Voltages	120/208/240/277/347/480 V

Mechanical and Housing	
Shape	Round
Initial Performance (IEC Compliant)	
Luminaire Lumens	3813
Efficacy	109 lm/W
Product Data	
Order product name	ClassicStyle Post Top LED (VLR), 30 LED, Type V, 4000K
Commercial Code	VLR-30L350NW-G1-5

## ClassicStyle Post Top LED (VLR)

<b>Order code</b>	VLR-30L350NW-G1-5
<b>Catalog Number Description</b>	ClassicStyle Post Top LED (VLR), 30 LED, Type V, 4000K
<b>Service / Spec Smart</b>	-

<b>Material Nr. (12NC)</b>	LUM70003796
----------------------------	-------------

