



# ClassicStyle Post Top LED (VLR)

## ClassicStyle Post Top LED with CAGE and House Side Shield (VLR-CAGE-HS), 29 LED, Type III, 4000K

ClassicStyle Post Top LED with CAGE and House Side Shield (VLR-CAGE-HS), 29 LED, Type III, 4000K - 75 lm/W

Now you can enjoy high-performing, energy-saving LED technology without worrying about the harsh glare or pixelization that can occur with LED luminaires. With the full, comfortable glow of new Philips Lumec ClassicStyle Luminaires with ClearGuide Technology, you can breathe new life into nighttime city spaces, strengthen a community bond, and enhance a sense of security throughout the night. This state-of-the-art, outdoor urban post top luminaire use a revolutionary, unique, vertically-oriented light engine that creates transparency during the day; while at night, the center comes to life with full illumination, and free from the glare typically found in standard LED technologies. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

### Product data

General Information		Mechanical and Housing	
Lamp Source Code	LED	Shape	Round
Color Temperature	4000K	Initial Performance (IEC Compliant)	
Photometric Distribution Type	Type III	Luminaire Lumens	5660
Mounting	Pole Top Pole Arm	Efficacy	75 lm/W
Operating and Electrical		Product Data	
Luminaire Input Watts	76	Order product name	ClassicStyle Post Top LED with CAGE and House Side Shield (VLR-CAGE-HS), 29 LED, Type III, 4000K
Voltages	120/208/240/277/347/480 V		

ClassicStyle Post Top LED (VLR)

Commercial Code	VLR-29L820NW-G1-3-CAGE-HS
Order code	VLR-29L820NW-G1-3-CAGE-HS
Catalog Number Description	ClassicStyle Post Top LED with CAGE and House Side Shield (VLR-CAGE-HS), 29 LED, Type III, 4000K

Service / Spec Smart	-
Material Nr. (12NC)	LUM70003871

