



HighFocus LED high mast (HFL)

HighFocus, 92 LED, Type V Wide

HighFocus, 92 LED, Type V Wide - 98 lm/W

Philips Lumec HighFocus LED high mast luminaires provide an energy saving, lowmaintenance solution that provides managers and work crews with the freedom to focus on other tasks. HighFocus LED features scalable lumen packages and offers up to 97,389 lumens.

Product data

General Information	
Lamp Source Code	LED
Color Temperature	4000K
CRI	70
Photometric Distribution Type	Type V
Mounting	Pole Arm
Operating and Electrical	
Luminaire Input Watts	320
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Square

Initial Performance (IEC Compliant)	
Luminaire Lumens	31223
Efficacy	98 lm/W
Product Data	
Order product name	HighFocus, 92 LED, Type V Wide
Commercial Code	HFL-92L-1050-NW-G1-5W
Order code	HFL-92L-1050-NW-G1-5W
Catalog Number Description	HighFocus, 92 LED, Type V Wide
Service / Spec Smart	-
Material Nr. (12NC)	LUM70004107