



RoadStar LED architectural roadway medium (GPLM-G2)

RoadStar, Medium Version, 80 LED, Type II Short

RoadStar, Medium Version, 80 LED, Type II Short - 117 lm/W

Stand out from the crowd with a striking design statement. Philips Lumec outdoor luminaires embody the epitome of sophisticated aesthetics, precision engineering and uncompromising quality, and the next generation Philips Lumec RoadStar LED architectural roadway luminaires are no exception. With two luminaire sizes and a wide range of options, RoadStar luminaires create an unrivaled crossroad of artistic style and high-performance functionality, so your design can make a powerful impact in any outdoor area.

Product data

General Information		Mechanical and Housing	
Lamp Source Code	LED	Shape	Rectangular
Color Temperature	4000K	Initial Performance (IEC Compliant)	
CRI	70	Luminaire Lumens	20409
Photometric Distribution Type	Type II	Efficacy	117 lm/W
Mounting	Pole Arm	Product Data	
Operating and Electrical		Order product name	RoadStar, Medium Version, 80 LED, Type II Short
Luminaire Input Watts	174	Commercial Code	GPLM-80L700NW-G2-R2S
Voltages	UNIV-HVU	Order code	GPLM-80L700NW-G2-R2S
		Catalog Number Description	RoadStar, Medium Version, 80 LED, Type II Short

RoadStar LED architectural roadway medium (GPLM-G2)

Service / Spec Smart	-
Material Nr. (12NC)	LUM70005177

