



Renaissance pendant - large (RN20-RN30)

Renaissance, 250 HPS, Type III, Medium, SemiCutoff

Renaissance, 250 HPS, Type III, Medium, SemiCutoff

Designed to exceed the aesthetic expectations of city planners, lighting designers, and other outdoor lighting professionals, the Renaissance stands as a tribute to history. The Renaissance mixes refinement together with ambition. The design reflects and evokes late 19th and early 20th century styling and is perfectly suited for most urban and rural areas. The state-of-the-art technology inside provides exceptional photometric performance, a long lifespan, and ease of maintenance. The Renaissance luminaire, now available with the LEDgine platform, offers high output for parking lots and high density street lighting. When powered by LEDgine you can save up to 60% in energy costs. It replaces up to 250W HPS which is equivalent up to 90 lumen per watt. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	250
Photometric Distribution Type	Type III
Mounting	Pole Arm

Operating and Electrical	
Voltages	120/208/240/277/347/480 V

Mechanical and Housing	
Shape	Round

Product Data	
Order product name	Renaissance, 250 HPS, Type III, Medium, SemiCutoff
Commercial Code	RNS-250HPS-THA3-GL
Order code	RNS-250HPS-THA3-GL
Catalog Number Description	Renaissance, 250 HPS, Type III, Medium, SemiCutoff
Service / Spec Smart	-
Material Nr. (12NC)	LUM70006732

Renaissance pendant - large (RN20-RN30)

