



Ancestra LED post top (AT10-AT20-AT30-AT40)

Ancestra 32 LED, Type 3, Flat Lens

Ancestra 32 LED, Type 3, Flat Lens - 92 lm/W

Its' eye-catching design will set your project apart. The Philips Lumec Ancestra LED post top and pendant luminaires present a new twist on an old-fashioned design. By combining the best aspects of past and present forms with the best that modern technology has to offer, the Ancestra luminaires epitomize Philips Lumec's design philosophy beautifully: to combine the best technology with an elegant design. Equipped with an optional copper cupola, a decorative cage, and crown accents, the result is a luminaire that complements any project with rustic flair and modern appeal without sacrificing photometric quality.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	5003
Color Temperature	4000K	Efficacy	92 lm/W
CRI	70		
Photometric Distribution Type	Type III		
Mounting	Pole Top Pole Arm		
Operating and Electrical		Product Data	
Luminaire Input Watts	54	Order product name	Ancestra 32 LED, Type 3, Flat Lens
Voltages	120/208/240/277/347/480 V	Commercial Code	ATx-55W32LED4K-G2-LE3F
Mechanical and Housing		Order code	ATx-55W32LED4K-G2-LE3F
Shape	Round	Catalog Number Description	Ancestra 32 LED, Type 3, Flat Lens
		Service / Spec Smart	-
		Material Nr. (12NC)	LUM70008009