



Ancestra post top (AT10-AT20-AT30-AT40)

Ancestra, 100 HPS, Type II, Short, Cutoff, Flat Lens

Ancestra, 100 HPS, Type II, Short, Cutoff, Flat Lens

Built to perform, its' eye-catching design will set your project apart. The Ancestra luminaire presents a new twist on an old-fashioned design. By combining the most popular aspects of past and present forms with the best that modern technology has to offer, the Ancestra epitomizes Philips Lumec's design philosophy beautifully: to combine superior LED technology with an elegant design.

[Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information

Lamp Source Code	HPS
Lamp Watts	100
Photometric Distribution Type	Type II
Mounting	Pole Top Pole Arm

Operating and Electrical

Voltages	120/208/240/277/347/480 V
----------	---------------------------

Mechanical and Housing

Shape	Round
-------	-------

Product Data

Order product name	Ancestra, 100 HPS, Type II, Short, Cutoff, Flat Lens
Commercial Code	ATx-100HPS-SG3
Order code	ATx-100HPS-SG3
Catalog Number Description	Ancestra, 100 HPS, Type II, Short, Cutoff, Flat Lens
Service / Spec Smart	-
Material Nr. (12NC)	LUM70008104