



Transit LED pendant (TR20)

Transit 32 LED, Type 2, Flat Lens

Transit 32 LED, Type 2, Flat Lens - 98 lm/W

The versatility and character of the Philips Lumec Transit LED post top and pendant luminaires is clear. Combining stunning industrial looks with outstanding photometric performance, the Transit luminaires blend modern and traditional style with leading-edge engineering that have made Philips Lumec luminaires the perfect choice for effective urban area lighting. Comfortable at any mounting height with a broad selection of optics, style options and lumen outputs make the Transit a sensible choice for your project's lighting needs.

Product data

General Information		Initial Performance (IEC Compliant)	
Lamp Source Code	LED	Luminaire Lumens	5336
Color Temperature	3000K	Efficacy	98 lm/W
Photometric Distribution Type	Type II		
Mounting	Suspended Pole Arm		
Operating and Electrical		Product Data	
Luminaire Input Watts	54	Order product name	Transit 32 LED, Type 2, Flat Lens
Voltages	120/208/240/277/347/480 V	Commercial Code	TR20-55W32LED3K-G2-LE2F
		Order code	TR20-55W32LED3K-G2-LE2F
		Catalog Number Description	Transit 32 LED, Type 2, Flat Lens
		Service / Spec Smart	-
		Material Nr. (12NC)	LUM70009367
Mechanical and Housing			
Shape	Round		