



Transit Post Top (TR10)

Transit, 70 HPS, Type II, Medium, Cutoff, Sag Lens

Transit, 70 HPS, Type II, Medium, Cutoff, Sag Lens

Combining state-of-the-art photometric performance with outstanding ease-of-maintenance the decorative Transit luminaires are designed to last in even the most demanding environments. The versatility and character of the Transit luminaire is clear. Combining stunning good looks with outstanding photometric performance, the Transit incorporates the cutting edge photometrics and ease of maintenance that have made Philips Lumec luminaires the perfect choice for effective area lighting. Equipped with the optional LifeLED the Transit's standard dark-sky friendly full cut-off optics turn this versatile product into one of the most environmentally responsible luminaires available on the market. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	70
Photometric Distribution Type	Type II
Mounting	Pole Top
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	Transit, 70 HPS, Type II, Medium, Cutoff, Sag Lens
Commercial Code	TR10-70HPS-SCB3M
Order code	TR10-70HPS-SCB3M
Catalog Number Description	Transit, 70 HPS, Type II, Medium, Cutoff, Sag Lens
Service / Spec Smart	-
Material Nr. (12NC)	LUM70009590