



Transit Pendant (TR20)

Transit, 150 HPS, Type III, Medium, Cutoff

Transit, 150 HPS, Type III, Medium, Cutoff

Combining state-of-the-art photometric performance with outstanding ease-of-maintenance the decorative Transit luminaires are designed to last in even the most demanding environments. The versatility and character of the Transit luminaire is clear. Combining stunning good looks with outstanding photometric performance, the Transit incorporates the cutting edge photometrics and ease of maintenance that have made Philips Lumec luminaires the perfect choice for effective area lighting. Equipped with the optional LifeLED the Transit's standard dark-sky friendly full cut-off optics turn this versatile product into one of the most environmentally responsible luminaires available on the market. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

Product data

General Information	
Lamp Source Code	HPS
Lamp Watts	150
Photometric Distribution Type	Type III
Mounting	Pole Arm
Operating and Electrical	
Voltages	120/208/240/277/347/480 V
Mechanical and Housing	
Shape	Round

Product Data	
Order product name	Transit, 150 HPS, Type III, Medium, Cutoff
Commercial Code	TR20-GRD-150HPS-SHA3M-ACDR
Order code	TR20-GRD-150HPS-SHA3M-ACDR
Catalog Number Description	Transit, 150 HPS, Type III, Medium, Cutoff
Service / Spec Smart	-
Material Nr. (12NC)	LUM70009674