



# L40U LED post top (L40U)

L40U Post Top LED 48 LED, Type IV, 530mA, Clear Globe 4000K

L40U Post Top LED 48 LED, Type IV, 530mA, Clear Globe 4000K - 68 lm/W

The L40U luminaires feature a one-piece square tapered cast aluminum housing, with a sealed optical system. The cast-aluminum hood includes a photoelectrical hiding decorative finial, assembled on the housing using two built-in hood hinges. [Lumec3D: Online 3D Configurator](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

## Product data

<b>General Information</b>		<b>Efficacy</b>	
Lamp Source Code	LED	68 lm/W	
Color Temperature	4000K	<b>Product Data</b>	
CRI	70	Order product name	L40U Post Top LED 48 LED, Type IV, 530mA, Clear Globe 4000K
Photometric Distribution Type	Type IV	Commercial Code	L40U-80W48LED4K-G2-C-LE4-HS
Mounting	Pole Top Pole Top Pole Top	Order code	L40U-80W48LED4K-G2-C-LE4-HS
<b>Operating and Electrical</b>		Catalog Number Description	L40U Post Top LED 48 LED, Type IV, 530mA, Clear Globe 4000K
Luminaire Input Watts	80	Service / Spec Smart	-
Voltages	120/208/240/277 V	Material Nr. (12NC)	LUM70012287
<b>Mechanical and Housing</b>			
Shape	Square		
<b>Initial Performance (IEC Compliant)</b>			
Luminaire Lumens	5550		

L40U LED post top (L40U)

