



SMS Surface Mount

Durable Surface / Valance mount fluorescent available with 1 lamp T5.

Durable Surface / Valance mount fluorescent available with 1 lamp T5.

Designed for smaller, tight spaces or to be hidden from sight in valance or under-shelf applications, the SMS performs perfectly in areas requiring high light level delivery. Wide opening fixture mouth with optional reflectors offer great light spread and throw with the use of a single lamp. This fixture is available in several different lengths that meet custom case design criteria. Most notable about this fixture is the heavy wireguard that can be affixed to the front fixture opening. This adds an additional safety feature offering protection for the lamp in tight design spaces. The standard SMS includes a Standard White Reflector, but Enhanced Specular, bright white and Amwhite reflectors are available upon request for increased distribution and efficiency. Applications include cove lighting, display boxes, valances, specialty wall wash applications, shelving units, cabinetry, store displays and anywhere space is limited and resistance to impact is important.

Product data

General Information		Order code	SMS 124 UV 1PS E
Lamp Source Code	FLU	Catalog Number Description	Durable Surface / Valance mount fluorescent available with 1 lamp T5.
Number of Lamps	1	Service / Spec Smart	-
Product Data		Material Nr. (12NC)	OPT00000201
Order product name	Durable Surface / Valance mount fluorescent available with 1 lamp T5.		
Commercial Code	SMS 124 UV 1PS E		