



SR Strip Retrofit Kit

Strip Retrofit Kit available with 1 lamp T5 or T8.

Strip Retrofit Kit available with 1 lamp T5 or T8.

The SR strip retrofit kit is designed to offer the end user a cost effective way to increase the efficiency and lumen output of existing strip fixtures. Custom fabricated for the existing channel width, the SR conversion kit is easy to install and provides for high efficiency lighting. Applications include distribution, warehouse, aisle lighting, retail applications and virtually anywhere existing strip fixtures are currently in use. SR retrofit kits are available with a variety of lamp and reflector combinations allowing the customer to design the SR system to meet or exceed existing light levels and customize the “look” to match their specific needs. Philips Optimum recommends the coupling of the Enhanced Specular reflector with high lumen T8 lamps as a way to maximize lumen output and fixture efficiency. The SR socket bar retrofit is designed for easy installation in existing strip fixtures.

Product data

General Information		Order code	
Lamp Source Code	FLU	SR 132 UV 1PS E	
Number of Lamps	1	Catalog Number Description	
Product Data		Strip Retrofit Kit available with 1 lamp T5 or T8.	
Order product name	Strip Retrofit Kit available with 1 lamp T5 or T8.	Service / Spec Smart	
Commercial Code	SR 132 UV 1PS E	-	
		Material Nr. (12NC)	
		OPT00000206	