



SRSB Strip Socket Bar Retrofit Kit

Socket bar Retrofit Kit available with 2 lamp T5 or T8.

Socket bar Retrofit Kit available with 2 lamp T5 or T8.

The SRSB socket bar retrofit kit is designed to offer the end user a cost effective way to increase the efficiency and lumen output of existing strip fixtures. Custom fabricated for the existing channel width or ordered with a universal adjustable socket bar, the SRSB conversion kit is easy to install and provides for high efficiency lighting. Applications include distribution, warehouse, aisle lighting and retail applications. SRSB retrofit kits are available with a variety of lamp and reflector combinations allowing the customer to design the SRSB system to meet or exceed existing light levels and customize the “look” to match their specific needs. Philips Optimum recommends the coupling of the Enhanced Specular reflector with high lumen T8 lamps as a way to maximize lumen output and fixture efficiency. The SRSB socket bar retrofit is designed for easy installation in existing strip fixtures.

Product data

General Information		Order code	SRSB 232 UV 1PS E
Lamp Source Code	FLU	Catalog Number Description	Socket bar Retrofit Kit available with 2 lamp T5 or T8.
Number of Lamps	2	Service / Spec Smart	-
Product Data		Material Nr. (12NC)	OPT00000210
Order product name	Socket bar Retrofit Kit available with 2 lamp T5 or T8.		
Commercial Code	SRSB 232 UV 1PS E		