



WPM Wall Pack Medium

HPS, 100W, 120V, w/Lamp, Wall-Pack

HPS, 100W, 120V, w/Lamp, Wall-Pack

The Wallprism Series includes four different sized surface mount HID/CF luminaires for security, accent and perimeter lighting. A patented catadioptric refractor redirects light to minimize glare, aligns optical center of lens and lamp for symmetrical light distribution. Sizes and maximum wattage range from WNPS (100W), WPM (300W), WP (500) and DB (400). Select models include high lumen output LEDs with 50,000 lifetime operating hours and induction that provides low maintenance and 100,000 lifetime operating hours.

Product data

General Information	
Lamp Source Code	High Pressure Sodium
Lamp Watts	100
Number of Lamps	1
Photometric Distribution Type	Type IV
Mounting	Wall
Operating and Electrical	
Voltages	120 V

Product Data	
Order product name	HPS, 100W, 120V, w/Lamp, Wall-Pack
Order code	WPM101NLXL-1
Material Nr. (12NC)	STU70000200
Catalog Number	WPM101NLXL-1
Catalog Number Description	HPS, 100W, 120V, w/Lamp, Wall-Pack