



# F Series Floodlight

## F Series, 1000W PSMH, Diffused Reflector Very Wide

### F Series, 1000W PSMH, Diffused Reflector Very Wide

250-1500W HID industrial floodlight with seven year warranty, suitable for industrial and marine floodlighting, and illumination of port facilities, drilling platforms, petrochemical plants, mining operations, parking lots and athletic fields. Standard unit is ETL/cETL listed to the UL 1598 standard, suitable for Wet Locations. Available ETL/cETL listed to the UL 1598A standard - Marine Listing option (MF Series). Available ETL/cETL listed to the UL 844 standard - Hazardous Location Listing (HAZ option for MF Series). Dust-Tite housing. Standard unit constructed to IP65. MF Series, Marine Listing, constructed to IP66. The F series provides superior floodlighting performance with unmatched efficiencies and ballast life. The fixture and ballast are arranged as separate but integral components. Standard Stabilux lamp socket. Die-cast aluminum alloy housing with integrally cast heat dissipating fins and a built-in aiming device. Cast aluminum ballast base provides integral mastfitter, suitable for mounting to a 2-3/8 inch O.D. vertical pipe tenon. Alternate mounting methods include shock mounting bracket, recommended for areas subject to extreme vibration. Standard colors available. Custom colors may be specified. Marine grade finish available.

### Product data

General Information		Operating and Electrical	
Lamp Envelope Code	BT/ED/E-37	Voltages	120/208/240/277/480 V
Lamp Source Code	Pulse Start Metal Halide	Maximum Lamp Watts	1000
Lamp Watts	1000	Approval and Application	
Number of Lamps	1	Safety Listing	ETL
Photometric Distribution Type	Wide Throw		
Mounting	Pole Top		

# F Series Floodlight

Product Data	
Order product name	F Series, 1000W PSMH, Diffused Reflector Very Wide
Order code	FP-1000-C
Material Nr. (12NC)	WLU00000795

Catalog Number	FP-1000-C
Catalog Number Description	F Series, 1000W PSMH, Diffused Reflector Very Wide

