



Aktra Floodlight

AF, 1000W PSMH, A Reflector

AF, 1000W PSMH, A Reflector

Aktra 1000 floodlight luminaire features low-profile, heavy-duty housing that is suitable for a variety of floodlighting applications. AF1000 achieves precise cutoff to control glare and restrict spill light, and meets IES criteria for Cutoff distribution. A secondary element reflects high angle rays back into the beam to achieve a high beam. Housing is constructed of permanent mold aluminum alloy with integrally cast heat dissipating fins. Standard unit constructed to IP65. Marine listing unit available (MAF) constructed to IP66. ETL/cETL listed to the UL 1598 standard, suitable for Wet Locations. UL 1598A Marine Listing available.

Product data

General Information

Lamp Source Code	PS
Lamp Watts	1000
Number of Lamps	1
Mounting	Pole Top

Operating and Electrical

Voltages	120/208/240/277/480 V
----------	-----------------------

Product Data

Order product name	AF, 1000W PSMH, A Reflector
Commercial Code	AFP-1000-A
Order code	AFP-1000-A
Catalog Number Description	AF, 1000W PSMH, A Reflector
Service / Spec Smart	-
Material Nr. (12NC)	WLU70000113